

**Vernier depth gauge, Measuring range: 200mm****Order data**

Order number	418000 200
GTIN	4045197203588
Item class	41Z

Description**Version:**

Measuring beam and vernier with clearly engraved scales. Precision ground contact faces. Vernier satin chrome-plated.

Supplied with:

From size 500 in a case.

Technical description

Cross-section measuring beam	8×3 mm
Vernier length	39 mm
Measuring range	0 - 200 mm
Bridge length	100 mm
Graduation	1/20 mm
Measuring tip b	7 mm
Measuring tip a	5 mm
Packaging	Wallet
Measurement deviation E MPE	± 0.05 mm
Standard	ISO 13385
Measurement technology	analogue

Material	Stainless steel, INOX
all parts	hardened
Calibration	A1
Type of product	Depth gauge

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200
CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200