



## Slitting saw arbor, for saw blade $\varnothing$ d1: 20mm



### Order data

Order number	345510 20
GTIN	4045197698735
Item class	32X

### Description

#### Version:

Precisely tempered, ground on the external and internal  $\varnothing$ , shank to DIN 1835 B. Concentricity 0.01 mm. **For side lock arbor with bore  $\varnothing$  (d<sub>3</sub>) 20 or 25 mm.**

#### Application:

For holding slitting saws No. 175000 – 179820 with  $\varnothing$  (d<sub>1</sub>) from 20 – 100 mm and saw blade thicknesses from 0.2 – 6 mm.

#### Supplied with:

Arbor, clamping screw and intermediate ring.

### Technical description

$\varnothing$ d <sub>2</sub>	5 mm
$\varnothing$ d <sub>4</sub>	10 mm
for saw blade $\varnothing$ d <sub>1</sub>	20 mm
Length L	90 mm
A	40 mm
$\varnothing$ d <sub>3</sub>	20 mm
Type of product	Slitting saw arbor

### Accessories

Spare screw for slitting saw arbor for saw blade  $\varnothing$  d1 20  
mm

345566 20

Spare washer for slitting saw arbor for saw blade  $\varnothing$  d1 20  
mm

345561 20