

**Vernier depth gauge, Measuring range: 300mm****Order data**

Order number	418000 300
GTIN	4045197203595
Item class	41Z

Description**Version:**

Measuring beam and vernier with clearly engraved scales. Precision ground contact faces.
Vernier satin chrome-plated.

Supplied with:

From size 500 in a case.

Technical description

Graduation	1/20 mm
Bridge length	150 mm
Cross-section measuring beam	12×4 mm
Vernier length	39 mm
Measuring tip b	9 mm
Measuring range	0 - 300 mm
Measuring tip a	6 mm
Packaging	Wallet
Measurement deviation E MPE	± 0.08 mm
Standard	ISO 13385
Measurement technology	analogue

Material	Stainless steel, INOX
all parts	hardened
Calibration	A1
Type of product	Depth gauge

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300
CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300