



Slitting saw arbor, for saw blade \varnothing d1: 50mm



Order data

Order number	345510 50
GTIN	4045197698773
Item class	32X

Description

Version:

Precisely tempered, ground on the external and internal \varnothing , shank to DIN 1835 B. Concentricity 0.01 mm. **For side lock arbor with bore \varnothing (d₃) 20 or 25 mm.**

Application:

For holding slitting saws No. 175000 – 179820 with \varnothing (d₁) from 20 – 100 mm and saw blade thicknesses from 0.2 – 6 mm.

Supplied with:

Arbor, clamping screw and intermediate ring.

Technical description

for saw blade \varnothing d ₁	50 mm
\varnothing d ₃	25 mm
\varnothing d ₄	24.5 mm
Length L	136 mm
A	78 mm
\varnothing d ₂	13 mm
Type of product	Slitting saw arbor

Accessories

Spare washer for slitting saw arbor for saw blade Ø d1 50
mm

345561 50

Spare screw for slitting saw arbor for saw blade Ø d1 50
mm

345566 50