



Vernier hook depth gauge, Measuring range: 200mm



Order data

Order number	418500 200
GTIN	4045197203694
Item class	41Z

Description

Version:

Vernier satin chrome-plated. Measuring beam and vernier with clearly engraved scales. Offset slim measuring beam with graduations on both sides. Can also be **used as normal vernier depth gauge** by reversing the measuring beam. Precision ground contact faces.

Supplied with:

Size 500L in a case.

Technical description

Vernier length	39 mm
Cross-section measuring beam	8×3 mm
Hook size b	5 mm
Bridge length	100 mm
Hook size a	20 mm
Graduation	1/20 mm
Measuring range	0 - 200 mm
Packaging	Wallet
Measurement deviation E MPE	± 0.05 mm
Standard	ISO 13385
Measurement technology	analogue

Material	Stainless steel, INOX
all parts	hardened
Calibration	A2
Type of product	Depth gauge

Services

DAkkS calibration Vernier hook depth gauge maximum measuring range 200 mm	021230 200
Calibration Vernier hook depth gauge maximum measuring range 200 mm	021220 200