



Vernier hook depth gauge, Measuring range: 500Lmm



Order data

Order number	418500 500L
GTIN	4045197203724
Item class	41Z

Description

Version:

Vernier satin chrome-plated. Measuring beam and vernier with clearly engraved scales. Offset slim measuring beam with graduations on both sides. Can also be **used as normal vernier depth gauge** by reversing the measuring beam. Precision ground contact faces.

Supplied with:

Size 500L in a case.

Technical description

Hook size b	10 mm
Hook size a	36 mm
Cross-section measuring beam	20×5 mm
Graduation	1/20 mm
Vernier length	39 mm
Measuring range	0 - 500 mm
Bridge length	250 mm
Packaging	sturdy box
Measurement deviation E MPE	± 0.1 mm
Standard	ISO 13385
Measurement technology	analogue

Material	Stainless steel, INOX
all parts	hardened
Calibration	A2
Type of product	Depth gauge

Services

Calibration Vernier hook depth gauge maximum measuring range 500 mm	021220 500
DAkkS calibration Vernier hook depth gauge maximum measuring range 500 mm	021230 500