

**Vernier double hook depth gauge, Measuring range: 300mm****Order data**

Order number	418520 300
GTIN	4045197203748
Item class	41Z

Description**Version:**

Measuring beam and vernier satin chrome-plated, with cleanly engraved scales. Precision ground contact faces.

Application:

Universal for depth measurements, distances, recesses, and grooves - particularly in bores. Please note dimension "a".

Technical description

Vernier length	39 mm
Graduation	1/20 mm
Cross-section measuring beam	10×3 mm
Measuring range	0 - 300 mm
Hook size a	23 mm
Bridge length	100 mm
Packaging	Wallet
Measurement deviation E MPE	± 0.08 mm
Standard	ISO 13385
Measurement technology	analogue
Material	Stainless steel, INOX

all parts	hardened
Calibration	A2
Type of product	Depth gauge

Services

Calibration Vernier hook depth gauge maximum measuring range 300 mm	021220 300
DAkkS calibration Vernier hook depth gauge maximum measuring range 300 mm	021230 300