

**HOLEX****Digital height gauge and marking-out system, Marking height: 600mm****Order data**

Order number	443850 600
GTIN	4045197204752
Item class	42D

**Description****Version:**

Digital height gauge and marking out system with fine adjustment. Sturdy stand with ground base.

Easily legible LCD display. Scriber carbide tipped.

**Function:**

Zeroing possible in any position.

Hold function (HOLD).

ABS / INC / TOL and SET.

**Supplied with:**

1 battery No. 081560 size 357, 1 carbide tipped scriber No. 443851.

**Technical description**

Marking height	600 mm
Base width	120 mm
Column cross section	30.9×10.7 mm
Base length	180 mm

Weight	3.4 kg
Error limit	0.07 mm
Scale divisions	0.0005 in
Scale divisions	0.01 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Calibration	E1
Type of product	Height gauge and marking device

### Services

Calibration Height gauge / height scriber maximum measuring range 1000 mm	024630 1000
Calibration of height gauges / vernier height gauges DAkkS maximum measuring range 1000 mm	024640 1000

### Accessories

Button cell / special battery Battery type 357	081560 357
Spare scriber, carbide tipped for marking heights 300 mm	443851 300
Spare scriber, carbide tipped for marking heights 600 mm	443851 600