

**External micrometer, Measuring range: 0-25mm****Order data**

Order number	420200 0-25
GTIN	4045197203762
Item class	42B

Description**Version:****Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Measuring range	0 - 25 mm
Spindle Ø	6.5 mm
Barrel Ø	18 mm
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm
Calibration	B1
Error limit	2 µm
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25
DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100