

**External micrometer, Measuring range: 75-100mm****Order data**

Order number	420200 75-100
GTIN	4045197203793
Item class	42B

Description**Version:****Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Measuring range	75 - 100 mm
Spindle Ø	6.5 mm
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm
Barrel Ø	18 mm
Calibration	B2
Error limit	3 µm
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

Accessories

Micrometer setting standard overall length 75 mm	421100 75
--	-----------