

**Large external micrometer 1/100 graduations, Measuring range: 25-150mm****Order data**

Order number	420770 25-150
GTIN	4045197203892
Item class	42B

**Description****Version:**

Hardened and ground measuring spindle. Precision lapped, carbide-tipped measuring faces. Locking by locking lever. Large barrel with 1/100 scale and ratchet. Lightweight external micrometers, hammer finish.

**Technical description**

Scale divisions	0.01 mm
Number of micrometer standards	5
Spindle Ø	8 mm
Number of measuring tips	5
Barrel Ø	25 mm
Spindle travel	25 mm
Micrometer barrel graduations	1/100 mm
Measuring range	25 - 150 mm
Calibration	S3
Standard	DIN 863

Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

### Services

Calibration External micrometers with extensions Measuring range 25-150 mm	020450 25-150
---	---------------

### Accessories

Micrometer setting standard overall length 50 mm	421100 50
--	-----------