

**Universal external micrometer, Measuring range: 0-25mm****Order data**

Order number	421750 0-25
GTIN	4045197203939
Item class	42B

Description**Version:**

Universal external micrometer with non-rotating spindle. Lapped measuring faces. Socket $\varnothing$ 5×15 mm. Steel frame forged and enamelled. Quick-change anvils. Zeroing by clamping slide sleeves.

Supplied with:

7 pairs of interchangeable anvils.

Technical description

Spindle pitch	0.5 mm
Micrometer barrel graduations	1/50 mm
Spindle $\varnothing$	8 mm
Measuring range	0 - 25 mm
Scale divisions	0.01 mm
Calibration	B1
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

Services

CalibrationExternal micrometer without setting dimension
maximum measuring range 25 mm

022000 25