

**Try square Accuracy class 2, Stock length: 600X300mm****Order data**

Order number	452600 600X300
GTIN	4045197205841
Item class	42F

Description**Version:**

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Technical description

Shank cross-section	40×8 mm
Right angle tolerance	0.08 mm
Stock length	600×300 mm
Calibration	F1
Standard	DIN 875
Accuracy	2

Type of product

Try squares