



Centring square, Stock length: 130mm



Order data

Order number	455000 130
GTIN	4045197205988
Item class	42F

Description

Version:

Precision steel version with mm graduation on the beam. Functional faces precision ground, remaining faces precision machined.

Application:

For marking the centre point of round plates and shafts. Centre is marked crosswise 2 - 3 times.

Technical description

Beam graduations	150 mm
for maximum shaft \varnothing	190 mm
Error limit	0.3 arc min.
Slide beam cross section	15×4.0 mm
Stock length	130 mm
Standard	Manufacturer's standard
Material	Stainless steel, INOX
Calibration	F5
Type of product	Centring square

Services

Calibration Centring, angle, and mitre squares maximum arm length 300

025850 300