

**External micrometer, Measuring range: 0-25mm****Order data**

Order number	423010 0-25
GTIN	4045197204066
Item class	42B

**Description****Version:**

With conical anvil for measuring the wall thickness of pipes and other curved parts. Measuring spindle with carbide-tipped anvils, anvil  $\varnothing$  8 mm, hardened. With hand temperature insulated frame, locking lever, and high quality ratchet.

**Technical description**

Micrometer barrel graduations	1/50 mm
Spindle $\varnothing$	6.5 mm
Measuring range	0 - 25 mm
Spindle pitch	0.5 mm
Scale divisions	0.01 mm
Calibration	B1
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

**Services**

DAkkS calibration External micrometer without setting  
dimension maximum measuring range 100 mm

022010 100

Calibration External micrometer without setting dimension  
maximum measuring range 25 mm

022000 25