



Horizontal toggle clamp with horizontal base, Type: 0



Order data

Order number	376625 0
GTIN	4045197229908
Item class	32S

Description

Version:

Captive contact screws.

With horizontal base for fixing to base plates etc.

Application:

For quick clamping and releasing of parts in series production or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Hole spacing e: 11.2 mm

Hole spacing f: 16 mm

Bore Ø d: 4.3 mm

Clamping height H: 8 mm

Clamping force P1: 230 N

Clamping force P2: 380 N

Technical description

overall height	17 mm
overall length	77 mm
Contact screw	M4×20 mm
Bore Ø d	4.3 mm
Clamping force P1	230 N

Hole spacing e	11.2 mm
Hole spacing f	16 mm
Clamping force P2	380 N
Type	376625 0
Clamping height H	8 mm
Type of product	Horizontal toggle clamp