



## Horizontal toggle clamp with horizontal base, Type: 2



### Order data

Order number	376625 2
GTIN	4045197229922
Item class	32S

### Description

#### Version:

Captive contact screws.

With horizontal base for fixing to base plates etc.

#### Application:

**For quick clamping and releasing of parts in series production** or for installation as part of special clamping jigs. Suitable for clamping during drilling, reaming, grinding, bending, welding, fitting etc.

Hole spacing e: 26 mm

Hole spacing f: 25 mm

Bore Ø d: 5.5 mm

Clamping height H: 24 mm

Clamping force P1: 1200 N

Clamping force P2: 1400 N

### Technical description

Hole spacing e	26 mm
Contact screw	M6×40 mm
Hole spacing f	25 mm
Clamping force P1	1200 N
Bore Ø d	5.5 mm

overall length	163 mm
Clamping force P2	1400 N
overall height	54 mm
Type	376625 2
Clamping height H	24 mm
Type of product	Horizontal toggle clamp