



Internal micrometer, Measuring range: 10-12mm



Order data

Order number	428990 10-12
GTIN	4045197276339
Item class	42B

Description

Version:

Satin chrome plated scales and operating parts (from \varnothing 12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from \varnothing 12 with carbide jaws).

Supplied with:

Setting ring (for adjustment) and extension.

Optional extras:

Extension No. 428993, setting rings No. 484030.

Technical description

Measuring range	10 - 12 mm
Setting ring \varnothing	10 mm
Measuring depth with extension	154 mm
Dimension a	1.5 mm
Standard measuring depth	54 mm
Error limit	0.005 mm
Scale divisions	0.001 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration 3-point internal micrometer maximum measuring range 100R mm	022500 100R
DAkkS calibration 3-point internal micrometer maximum measuring range 200R mm	022510 200R

Accessories

Extension for internal micrometer Type 6-12	428993 6-12
Setting ring DIN 2250 C Nominal size \varnothing 12 mm	484030 12
Setting ring DIN 2250 C Nominal size \varnothing 11 mm	484030 11
Setting ring DIN 2250 C Nominal size \varnothing 10 mm	484030 10