

Garant**Tape measure with viewing window, Band length: 2m**

Order data

Order number	462210 2
GTIN	4045197154101
Item class	41H

Description

Version:

- Shock-resistant plastic casing.
- Aluminium inlay on both work faces, giving exact contact surfaces for inside and outside measurement.
- Aluminium profiles resistant to heat and mechanical loads.
- Tape measure stove enamelled, with black characters. Cambered = non-buckling with sliding end hook (for inside and outside measurements). Sharp-contrast, abrasion-resistant rustproof scale.
- Graduations mm / mm (upper / lower edges).
- Viewing window scale reads in the same direction as the tape.

Technical description

Tape width	16 mm
Body height	63 mm
Body length	63 mm
Body width	24 mm

Band length	2 m
Standard	EG II
Calibration	G1
Type of product	Measuring tape

Services

CalibrationTape measure maximum length 2 m	026240 2
--	----------