



## Internal micrometer set, Measuring range: 6-12mm



### Order data

Order number	428991 6-12
GTIN	4045197276360
Item class	42B

### Description

#### Version:

Satin chrome plated scales and operating parts (from  $\varnothing$  12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from  $\varnothing$  12 with carbide jaws).

#### Supplied with:

Internal micrometers No. 428990, setting rings (for adjustment) and extension.

### Technical description

Number of setting rings	2
Setting ring $\varnothing$	8 / 10 mm
Number of micrometers	3
Measuring range	6 - 12 mm
Error limit	0.004 / 0.005 mm
Scale divisions	0.001 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	S6
Type of product	3-point internal micrometer

### Services

CalibrationInternal micrometer set Measuring range 6-12 mm	020550 6-12
--	-------------

### Accessories

Internal micrometer Measuring range 8-10 mm	428990 8-10
Setting ringDIN 2250 C Nominal size Ø 9 mm	484030 9
Setting ringDIN 2250 C Nominal size Ø 7 mm	484030 7
Setting ringDIN 2250 C Nominal size Ø 8 mm	484030 8
Extension for internal micrometer Type 6-12	428993 6-12
Internal micrometer Measuring range 10-12 mm	428990 10-12
Internal micrometer Measuring range 6-8 mm	428990 6-8
Setting ringDIN 2250 C Nominal size Ø 10 mm	484030 10