



## Internal micrometer set, Measuring range: 50-100mm



### Order data

Order number	428991 50-100
GTIN	4045197327994
Item class	42B

### Description

#### Version:

Satin chrome plated scales and operating parts (from  $\varnothing$  12 with carbide jaws). Self-centring micrometer head with 3 measuring jaws (from  $\varnothing$  12 with carbide jaws).

#### Supplied with:

Internal micrometers No. 428990, setting rings (for adjustment) and extension.

### Technical description

Number of setting rings	2
Number of micrometers	4
Measuring range	50 - 100 mm
Setting ring $\varnothing$	62 / 87 mm
Error limit	0.007 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue

Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

### Services

Calibration Internal micrometer set Measuring range 50-100 mm	020550 50-100
---	---------------

### Accessories

Setting ring DIN 2250 C Nominal size Ø 80 mm	484030 80
Setting ring DIN 2250 C Nominal size Ø 95 mm	484030 95
Extension for internal micrometer Type 50-100	428993 50-100
Setting ring DIN 2250 C Nominal size Ø 70 mm	484030 70
Internal micrometer Measuring range 62-75 mm	428990 62-75
Setting ring DIN 2250 C Nominal size Ø 55 mm	484030 55
Internal micrometer Measuring range 75-88 mm	428990 75-88
Internal micrometer Measuring range 50-63 mm	428990 50-63
Internal micrometer Measuring range 87-100 mm	428990 87-100