



Vernier caliper Vernier 1/20, Measuring range: 100mm



Order data

Order number	410200 100
GTIN	4045197302106
Item class	41Z

Description

Version:

Satin chromium plated anti-glare reading parts.
Locking screw at the top. Without inch graduation.

Supplied with:

Including thread table No. 412180 for caliper back.

Technical description

Packaging	Wallet
Scale divisions	0.05 mm
Jaw length	30 mm
Calibration	A1
Measuring range	0 - 100 mm
Graduation	1/20 mm
Standard	ISO 13385
Depth gauge	rectangular 2.2×1.0
Depth gauge available	yes
Measurement deviation E MPE	±0.05 mm
Locking	Locking screw at top

Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200
CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200