



Vernier caliper parallax-free with spring-loaded thumb-lock, Measuring range: 150mm



Order data

Order number	410650 150
GTIN	4045197304018
Item class	41Z

Description

Version:

Satin chromium plated anti-glare reading parts. Fine, high-contrast scale, precision lapped measuring faces. Flat vernier scale for **parallax-free reading**.
With thumb lock and sturdy flat depth gauge.

Technical description

Jaw length	40 mm
Packaging	sturdy box
Measuring range	0 - 150 mm
Scale divisions	0.05 mm
Calibration	A1
Graduation	1/20 mm
Graduation	1/128 in
Reversible reading	mm / inch
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3
Depth gauge available	yes
Measurement deviation E MPE	± 0.05 mm

Scale chrome plated	yes
Locking	Spring-loaded thumb-lock
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Synthetic leather case for vernier calipers	412500
Table for calipers	412180
Screw for depth gauge holder	412236