



## Vernier caliper Vernier 1/20, Measuring range: 300mm



### Order data

Order number	410200 300
GTIN	4045197519207
Item class	41Z

### Description

#### Version:

Satin chromium plated anti-glare reading parts.  
Locking screw at the top.

#### Supplied with:

Including thread table No. 412180 for caliper back.

### Technical description

Scale divisions	0.05 mm
Calibration	A1
Packaging	Wallet
Measuring range	0 - 300 mm
Jaw length	64 mm
Graduation	1/20 mm
Graduation	1/128 in
Reversible reading	mm / inch
Standard	ISO 13385
Depth gauge	rectangular 4.7×1.8
Depth gauge available	yes
Measurement deviation E MPE	± 0.08 mm

Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

### Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

### Accessories

Plastic case Type MS300	412470 MS300
-------------------------	--------------