



Vernier caliper Vernier 1/50 with rod type depth gauge, Measuring range: 150mm



Order data

Order number	410205 150
GTIN	4045197202949
Item class	41Z

Description

Version:

Satin chromium plated anti-glare reading parts.
Locking screw at the top.

Supplied with:

Including thread table No. 412180 for caliper back.

Technical description

Calibration	A1
Packaging	Wallet
Scale divisions	0.02 mm
Measuring range	0 - 150 mm
Jaw length	40 mm
Graduation	1/50 mm
Graduation	1/1000 in
Reversible reading	mm / inch
Standard	ISO 13385
Depth gauge	Ø 1.6
Depth gauge available	yes

Measurement deviation E MPE	±0.04 mm
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Synthetic leather case for vernier calipers	412500
---	--------