



Dial calipers, Type: 150/01



Order data

Order number	412350 150/01
GTIN	4045197203083
Item class	41Z

Description

Version:

Satin chrome-plated scale. Shock-proof, with protected rack. Precision dial indicator with rotating dial and locking screw. Readings of 1 mm on the beam, 1/100 mm on the round dial.

Technical description

Calibration	A1
Pointer revolution	1 mm
Measuring range	0 - 150 mm
Jaw length	40 mm
Reading (round dial)	0.01 mm
Measurement deviation E MPE	± 0.03 mm
Standard	ISO 13385
Depth gauge	rectangular 4.8×1.7
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Thread table	Calipers table

Type of product

Dial calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm

021000 200

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm

021010 200