

Garant**Burr Z5 – fine, Carbide, Type: A0820****Order data**

Order number	540400 A0820
GTIN	4045197521545
Item class	51D

Description**Version:**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape**(ZYA), **without end cut**.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Overall length	60 mm
Tooth type abbreviation	Z5
Head Ø	8 mm
Toothing grit designation	fine
Shape description	Cylindrical without end cut
Shape	A0820
Shank Ø	6 mm
Head length	20 mm
Series	Tooth configuration Z5
Tool material	Carbide

Type of product

Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		