

Garant**Burr Z FINE – very fine, Carbide, Type: C1225****Order data**

Order number	540440 C1225
GTIN	4045197679888
Item class	51D

Description**Version:**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Tooth type abbreviation	Z FINE
Overall length	65 mm
Head Ø	12 mm
Toothing grit designation	very fine
Shape	C1225
Shape description	Ball nose
Shank Ø	6 mm
Head length	25 mm
Series	Tooth configuration Z FINE
Tool material	Carbide

Type of product	Burr
-----------------	------

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		