


**Abrasive sleeve (A) 60 grit medium coarse, Sleeve Ø×Width of sleeve:  
22X20mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 553710 22X20  |
| GTIN         | 4045197240309 |
| Item class   | 52E           |

**Description****Version:**

**The rubber body of the abrasive sleeve holder expands at high speed to hold the abrasive sleeve in place.** The full width of the sleeve can be used, it does not slip and can be replaced quickly and easily (twist in the direction of slots when fitting/removing). Only compatible with abrasive sleeve holders.

Made of non-tearing, synthetic resin bonded material with long service life and good grit adhesion. Unsuitable for use with cooling lubricants.

**Aluminium oxide (A).****Application:**

Abrasive sleeves are predominantly used for surface grinding tasks which require the removal of large amounts of material – even at sharp edges.

**Suitable for :**

Abrasive sleeve holder No. 553600.

Grinding medium code: A

**Technical description**

|      |    |
|------|----|
| Grit | 60 |
|------|----|

|                      |                          |
|----------------------|--------------------------|
| Sleeve Ø             | 22 mm                    |
| Sleeve width         | 20 mm                    |
| Grit designation     | medium coarse            |
| Grinding media       | Standard Aluminium Oxide |
| Grinding medium code | A                        |
| Sleeve shape         | cylindrical              |
| Type of product      | Abrasive sleeve          |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|-------------------------------------------|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable only under restricted conditions |                |          |
| Steel < 55 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable only under restricted conditions |                |          |
| GG(G)                          | suitable only under restricted conditions |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |

## Accessories

Abrasive sleeve holder, slit, shank Ø 6 mm Head Ø×head length 22X20 mm

553600 22X20