

**Burr Z3 - medium, with chip breaker, HSS, Type: C1020****Order data**

Order number	540800 C1020
GTIN	4045197156082
Item class	52D

Description**Version:**

Shank \varnothing 6 mm.

HSS burrs for difficult vibration applications. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape	C1020
Head \varnothing	10 mm
Shape description	Ball nose
Overall length	60 mm
Shank \varnothing	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	20 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

