

Garant

Clamping toolholder PDNNL 63°, for indexable inserts DN., left-hand, Shank / insert size: 20/11mm



Order data

Order number	250613 20/11
GTIN	4045197861771
Item class	21T

Technical description

ISO code toolholder	PDNNR/L 2020K11
Shim pins pack	259044 4
Insert size	11 mm
Lever screw	259018 6
Head length L ₁	25 mm
Functional width L ₄	10 mm
suitable indexable insert	DN.. 1104..
Lever	259015 7
Shim punches pack	259047 3
Shank size	20 mm
Overall length L	125 mm
Shim	259031 7
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	63 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 7	259015 7
Lever screw Type 6	259018 6
Shim Type 7	259031 7
Set of shim pins 10 pieces Type 4	259044 4
Shim punches set 10 pieces Type 3	259047 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5