

Garant

Clamping toolholder PDNNL 63°, for indexable inserts DN., left-hand, Shank / insert size: 20/15mm



Order data

| | |
|--------------|---------------|
| Order number | 250613 20/15 |
| GTIN | 4045197861795 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-----------------|
| Overall length L | 125 mm |
| Head length L ₁ | 35 mm |
| Lever screw | 259018 7 |
| suitable indexable insert | DN.. 1506.. |
| Shank size | 20 mm |
| Shim punches pack | 259047 2 |
| Shim | 259031 28 |
| Insert size | 15 mm |
| ISO code toolholder | PDNNR/L 2020K15 |
| Lever | 259015 8 |
| Functional width L ₄ | 12 mm |
| Shim pins pack | 259044 2 |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 63 degrees |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|------------|
| Lever Type 8 | 259015 8 |
| Lever screw Type 7 | 259018 7 |
| Shim Type 28 | 259031 28 |
| Set of shim pins 10 pieces Type 2 | 259044 2 |
| Shim punches set 10 pieces Type 2 | 259047 2 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm | 674242 3 |