

Garant
**Clamping toolholder PSBNR 75°, for indexable inserts SN., right-hand,
Shank / insert size: 20/12mm**

Order data

Order number	251106 20/12
GTIN	4045197861924
Item class	21T

Technical description

Overall length L	125 mm
Shim pins pack	259044 2
Shim	259031 20
Lever screw	259018 2
Functional width L ₄	17 mm
Shim punches pack	259047 2
Head length L ₁	28 mm
suitable indexable insert	SN.. 1204..
Lever	259015 2
Insert size	12 mm
ISO code toolholder	PSBNR/L 2020K12
Shank size	20 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3