

Garant
**Clamping toolholder PSBNR 75°, for indexable inserts SN., right-hand,
Shank / insert size: 25/12mm**

Order data

Order number	251106 25/12
GTIN	4045197861931
Item class	21T

Technical description

Shim	259031 20
Shank size	25 mm
Head length L ₁	29 mm
Shim punches pack	259047 2
Shim pins pack	259044 2
Lever	259015 2
suitable indexable insert	SN.. 1204..
ISO code toolholder	PSBNR/L 2525M12
Overall length L	150 mm
Functional width L ₄	22 mm
Insert size	12 mm
Lever screw	259018 2
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3