

Garant
**Clamping toolholder PSBNR 75°, for indexable inserts SN., right-hand,
Shank / insert size: 32/15mm**

Order data

| | |
|--------------|---------------|
| Order number | 251106 32/15 |
| GTIN | 4045197861955 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-----------------|
| Shim pins pack | 259044 6 |
| Overall length L | 170 mm |
| Shim | 259031 37 |
| Head length L ₁ | 32 mm |
| Lever screw | 259018 11 |
| Insert size | 15 mm |
| Shank size | 32 mm |
| Shim punches pack | 259047 4 |
| suitable indexable insert | SN.. 1506.. |
| Lever | 259015 12 |
| Functional width L ₄ | 27 mm |
| ISO code toolholder | PSBNR/L 3232P15 |
| Standard | Works standard |
| Application type | right-hand |
| Through-coolant | no |
| Setting angle κ | 75 degrees |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |