

Garant
Clamping toolholder PSBNL 75°, for indexable inserts SN., left-hand, Shank / insert size: 20/12mm

Order data

Order number	251107 20/12
GTIN	4045197861979
Item class	21T

Technical description

Shank size	20 mm
Insert size	12 mm
ISO code toolholder	PSBNR/L 2020K12
Head length L ₁	28 mm
Shim	259031 20
Lever	259015 2
Overall length L	125 mm
Lever screw	259018 2
Functional width L ₄	17 mm
Shim punches pack	259047 2
Shim pins pack	259044 2
suitable indexable insert	SN.. 1204..
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3