

Garant

Clamping toolholder PSBNL 75°, for indexable inserts SN., left-hand, Shank / insert size: 32/19mm



Order data

Order number	251107 32/19
GTIN	4045197862013
Item class	21T

Technical description

suitable indexable insert	SN.. 1906..
Lever	259015 13
Functional width L ₄	27 mm
Shim pins pack	259044 7
Shim	259031 38
Lever screw	259018 13
Insert size	19 mm
Overall length L	170 mm
Shim punches pack	259047 5
Head length L ₁	39 mm
ISO code toolholder	PSBNR/L 3232P19
Shank size	32 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4