



Burr Z3 - medium, with chip breaker, HSS, Type: C1225



Order data

| | |
|--------------|---------------|
| Order number | 540800 C1225 |
| GTIN | 4045197156099 |
| Item class | 52D |

Description

Version:

Shank Ø 6 mm.

HSS burrs for difficult vibration applications. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

| | |
|---------------------------|------------------------|
| Shape description | ball nose |
| Overall length | 65 mm |
| Head Ø | 12 mm |
| Shape | C1225 |
| Shank Ø | 6 mm |
| Tooth type abbreviation | Z3 |
| Type of cut | with chip breaker |
| Toothing grit designation | medium |
| Head length | 25 mm |
| Series | Tooth configuration Z3 |
| Tool material | HSS |
| Type of product | Burr |

