

Garant**Burr Z1 - coarse, Carbide, Type: C1225****Order data**

Order number	540600 C1225
GTIN	4045197155801
Item class	51D

Description**Version:**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape	C1225
Toothing grit designation	coarse
Overall length	65 mm
Head Ø	12 mm
Tooth type abbreviation	Z1
Shape description	ball nose
Shank Ø	6 mm
Head length	25 mm
Series	Tooth configuration Z1
Tool material	Carbide

Type of product	Burr
-----------------	------

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
Wood	suitable only under restricted conditions		