

**Burr Z3 - medium, with chip breaker, HSS, Type: AS1225****Order data**

Order number	540800 AS1225
GTIN	4045197156044
Item class	52D

Description**Version:**

Shank Ø 6 mm.

HSS burrs for difficult vibration applications. **Cylindrical shape** (ZYAS), **with end cut**.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape	AS1225
Shape description	Cylindrical with end cut
Head Ø	12 mm
Overall length	65 mm
Shank Ø	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	25 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

