


**Burr Z3 - medium, with chip breaker, HSS, Type: L1230****Order data**

|              |               |
|--------------|---------------|
| Order number | 540800 L1230  |
| GTIN         | 4045197156228 |
| Item class   | 52D           |

**Description****Version:**

Shank Ø 6 mm.

HSS burrs for difficult vibration applications. **Round cone shape** (KEL).

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

|                           |                        |
|---------------------------|------------------------|
| Overall length            | 70 mm                  |
| Head Ø                    | 12 mm                  |
| Shape                     | L1230                  |
| Shape description         | Round cone             |
| Shank Ø                   | 6 mm                   |
| Tooth type abbreviation   | Z3                     |
| Type of cut               | with chip breaker      |
| Toothing grit designation | medium                 |
| Head length               | 30 mm                  |
| Series                    | Tooth configuration Z3 |
| Tool material             | HSS                    |
| Type of product           | Burr                   |

