

**Burr Z3 - medium, with chip breaker, HSS, Type: D1614****Order data**

Order number	540800 D1614
GTIN	4045197156143
Item class	52D

Description**Version:**

Shank Ø 6 mm.

HSS burrs for difficult vibration applications. **Ball shape** (KUD)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Overall length	60 mm
Shape	D1614
Shape description	ball
Head Ø	16 mm
Shank Ø	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	14 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

