

Garant

Steel boring bar A.. MVPNL 117,5°, for indexable inserts VN.., left-hand, Shank Ø / insert size: 25/16mm


Order data

Order number	251721 25/16
GTIN	4045197867179
Item class	21T

Technical description

Centre offset L_3	17 mm
Clamping height L_2	24 mm
Insert size	16 mm
Setting angle κ	117.5 degrees
Minimum pre-drill $\varnothing D_{\min}$	32 mm
Clamping claw	259038 4
ISO code toolholder	A25R MVPNR/L 16
Screw for clamp	259021 4
suitable indexable insert	VN.. 1604..
Overall length L	200 mm
Shim	259031 39
Shim screw	259025 3
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Screw for clamping claw Type 4	259021 4
Shim screw Type 3	259025 3
Shim Type 39	259031 39
Clamping claw Type 4	259038 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8