

Garant

**Steel boring bar A.. MVZNL 95°, for indexable inserts VN.., left-hand, Shank
Ø / insert size: 32/16mm**


Order data

Order number	251729 32/16
GTIN	4045197868275
Item class	21T

Technical description

Centre offset L_3	30 mm
Overhang L_1	96 mm
Clamping height L_2	31 mm
Shim	259031 39
Shim screw	259025 3
Minimum pre-drill $\varnothing D_{\min}$	48 mm
ISO code toolholder	A32S MVZNR/L 16
suitable indexable insert	VN.. 1604..
Insert size	16 mm
Setting angle κ	95 degrees
Overall length L	250 mm
Clamping claw	259038 2
Screw for clamp	259021 4
Usable depth T	14 mm
Shank $\varnothing D_s$	32 mm
Standard	Works standard

Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Screw for clamping claw Type 4	259021 4
Shim screw Type 3	259025 3
Shim Type 39	259031 39
Clamping claw Type 2	259038 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8