

Garant**Face mill arbor with cooling channel bore, HSK-A 63 A = 130, Spigot Ø d1: 27mm****Order data**

Order number	306566 27
GTIN	4045197870186
Item class	31A

Description**Version:**

- **Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.**
- **With Balluff/RFID chip bore.**
- **Increased collar contact surface.**
- **HSK mating faces machined.**

With **cooling channel bores.**

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw.

Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

Technical description

External Ø D	60 mm
Overhang dimension A	130 mm
Spigot Ø d ₁	27 mm
Spare milling cutter lock screw No. 309860 / 309861	27
Suitable toggle spanner No. 309840	27

Milling mandrel length L_4	21 mm
Clamping $\varnothing D_1$	27 mm
Adapter	HSK-A 63 A = 130
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-3
Arbor standard	DIN 69893
Shape	A
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel $\varnothing 27$ mm	309840 27
Milling cutter lock screw for mandrel $\varnothing 27$ mm	309860 27
Bolt for T-nuts for spigot $\varnothing D1 27$ mm	309896 27
Half-round T-nut for face mill arbors For size 27	309898 27