

Garant**Flap wheel M14 Fabric (A), Ø 125 mm×20 mm, Grit: 80****Order data**

Order number	566350 80
GTIN	4045197345820
Item class	51M

Description**Version:**

Strips arranged in a fan form around the axis of the tool. **M14 direct mounting**. Extremely flexible.

Abrasive cloth, regular aluminium oxide (A).

Application:

For fine abrasion of convex surfaces.

Technical description

Grit	80
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Disc Ø	125 mm
Disc thickness	20 mm

Product name attribute	Ø 125 mm×20 mm
Thread	M14
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Flap wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		