

Garant**CNMG 120404, Grade: HB7035-1**

Order data

Order number	250156 HB7035-1
GTIN	4045197873859
Item class	21G

Description

CN.G 120404 HB7035-1 Grade: HB7035-1
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 8 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 100 - 320 m/min

Technical description

Feed f	0.2 - 0.5 mm/rev.
Grade	HB7035-1
Cutting depth a_p	0.5 - 8 mm
Cutting speed v_c main application	100 - 320 m/min
Chip breaker	SM
Main application	P

Corner radius	0.4 mm
Cutting conditions	heavily interrupted
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	CNMG 120404
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning