

**HOLEX****Roll of abrasive fleece, 115 mm × 10 m, Fleece structure: 1000****Order data**

|              |               |
|--------------|---------------|
| Order number | 556115 1000   |
| GTIN         | 4045197241740 |
| Item class   | 52M           |

**Description****Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding.

**Advantage:**

- **Adapts to the component shape.**
- **The open structure prevents clogging and reduces heat development.**
- **Even and reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

**Application:**

Can be used by hand, on hand block No. 556020 or on an orbital sander. **Fine / very fine:** for cleaning delicate surfaces, for removing light scratches on metals. Also suitable for applying fine / very fine matt finishes to steels and non-ferrous metals.

Iron, sulphur and chlorine constituents: < 0.1 %

Grit equivalent: 600 - 1000

Grit designation: very fine

Version: S Ultra Fine

Colour: grey

**Technical description**

|   |                         |
|---|-------------------------|
| Colour                                  | grey                    |
| Grit designation                        | very fine               |
| Fleece structure                        | 1000                    |
| Grit equivalent                         | 600 - 1000              |
| Version                                 | S Ultra Fine            |
| Iron, sulphur and chlorine constituents | < 0.1 %                 |
| Roller width                            | 115 mm                  |
| Roll length                             | 10 m                    |
| Product name attribute                  | 115 mm × 10 m           |
| Type of product                         | Roll of abrasive fleece |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable                                  |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable                                  |                |          |
| GG(G)                          | suitable                                  |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| Stone                          | suitable only under restricted conditions |                |          |
| Paint                          | suitable                                  |                |          |
| Uni                            | suitable                                  |                |          |

|             |   |
|-------------|---|
| wet maximum | suitable only under restricted conditions |
| dry         | suitable                                  |

---

## Accessories

|            |        |
|------------|--------|
| Hand block | 556020 |
| Mandrel    | 556030 |