

**Garant**
**Eco toolholder axial single, right-hand, HSK-T 63, for toolholder square: 25mm**

**Order data**

Order number	318620 25
GTIN	4045197889379
Item class	31G

**Description**
**Version:**

With adjustable cooling nozzle with internal thread.

**GARANT** - Optimisation of tool life, better surface finishes, increased process reliability and increased productivity due to GARANT Eco.

**Application:**

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

**Note:**

With pass-through shim. Suitable for toolholders with shank 20 **and** 25 mm.

**Technical description**

Clamping length L <sub>1</sub>	88 mm
for toolholder square	25 mm
External Ø D	102 mm
Overhang dimension A	130 mm
B	40 mm
Adapter	HSK-T 63
Arbor standard	ISO 12164-3

Through-coolant	yes
Type of product	Pin vice