

**Garant****Eco toolholder axial single, left-hand, HSK-T 63, for toolholder square: 25mm****Order data**

Order number	318621 25
GTIN	4045197893246
Item class	31G

**Description****Version:**

With adjustable cooling nozzle with internal thread.

**GARANT** - Optimisation of tool life, better surface finishes, increased process reliability and increased productivity due to GARANT Eco.

**Application:**

For mounting ISO toolholders with square shanks.

For mounting ISO toolholders with square shanks.

**Note:**

With pass-through shim. Suitable for toolholders with shank 20 **and** 25 mm.

**Technical description**

Overhang dimension A	130 mm
External Ø D	102 mm
B	40 mm
Clamping length L <sub>1</sub>	88 mm
for toolholder square	25 mm
Adapter	HSK-T 63
Arbor standard	ISO 12164-3
Through-coolant	yes

Type of product

Pin vice